



Transformer

by ABB



1M000000

Catalog Number


Type QL

9T76H9873G13

45.0 KVA 60 HZ 3 PH 4.5 % IMP
40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

JUMPER
CONNECTION
TAP VOLTS

1 505
2 493
3 480
4 470
5 455
6 443
7 431



NET WGT
640 LB
290.3 Kg
88644




H373C
NOG
070221

INSPECTION
&
FINAL TEST
N127!

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 208 VOLTS (LINE-LINE)
120 VOLTS (LINE-NEUTRAL)

COIL TAP ARRANGEMENT



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD
9T18Y4317G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP01
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**

ASSEMBLED IN MEXICO

Note:

Outline: 303B431SLP073

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



2M000000



3M000000