



Transformer

Catalog Number
9T76H9874G03


75.0 KVA 60 HZ 3 PH 3.5 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C Type: QL

Note: Design is based on 75.00KVA & 115C Rise 3.3% Imp.


PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 208 VOLTS (LINE-LINE)
 120 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE



JUMPER CONNECTION TAP	VOLTS
1-2	503
2-3	494
3-4	480
4-5	468
5-6	455
6-7	442
7-8	433

COIL TAP ARRANGEMENT



NET WGT 990 LB 449.1 Kg

092216 N639! H374C
66215 NOG

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R. ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18V4317G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL



LISTED 769G

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Outline: 3038431SLP074 INSPECTION & FINAL TEST
Assembled in Mexico N639!

GE Energy Industrial Solutions

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



1M0000000



3M0000000