



GE Consumer & Industrial
 Specialty Transformer
 PO Box 1701
 Ft. Wayne, IN 46801
 (260) 439-2000

GE MODEL #:
9T76H9874G13

Underwriters' Laboratories Inc Listed

RATING:

CU 3PH 60HZ 75.0KVA 480 +2,-4(2.5%TAPS) 208Y/120

Frame = M374C

Temp. Rise (C) = 110 Insulation System = 220C

Average Sound Level (dB) = 50

LOSS DATA @ 100% LOAD:

Core Loss or No Load Loss @ 100% voltage (Watts) =	153.0
Impedance Loss or Coil Loss @ Rise + 20C reference (Watts) =	<u>2160.0</u>
Total Loss @ Rise + 20C reference (Watts) =	2313.0

DIELECTRIC AND PRODUCTION TESTING:

Induce Test @ Twice rated voltage 400 Hz per ANSI C89.2 and NEMA ST-20

Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz 60 Sec.

Hipot Test for Low Voltage winding to High Voltage and Ground @ 2500 volts 60 Hz 60 Sec.

Polarity additive in accordance with ANSI C89.2 and NEMA ST-20

EFFICIENCY:

Load (%)	NEMA TP1 Efficiency (%)
16.67	98.4
25	98.6
35	98.7
50	98.5
75	98.1
100	97.6

IMPEDANCE:

Impedance at reference temperature of Rise + 20C (Calculated).

%R =	2.88
%X =	2.00
%Z =	3.51

REGULATION:

Regulation at reference temperature of Rise + 20C (Calculated).

PF	Regulation (%)
1.0	2.82
0.8	3.39

NON-LINEAR LOAD EFFICIENCY (K7):

Load (%)	Efficiency (%)	Windings reference temperature C
16.67	98.3	57
25	98.5	65
35	98.4	75
50	98.1	89
75	97.5	112
100	96.7	135

Load profile considered for energy efficiency calculation

Harmonic	Load current (A)
1	175.50
3	83.13
5	62.19
7	37.97
9	16.11
11	2.46
13	6.47
15	8.11