



# Transformer

by ABB



\*1M000000\*

Catalog Number  
9T76H9875G03


Type QL

112.5 KVA    60 HZ    3 PH    2.3 % IMP  
40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C

JUMPER CONNECTION TAP VOLTS

1-2	504
2-3	490
3-4	480
4-5	467
5-6	458
6-7	444
7-8	430

PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 208 VOLTS (LINE-LINE)  
120 VOLTS (LINE-NEUTRAL)




NET WGT  
1845 LB  
836.9 Kg  
85794



H375C  
NOG  
030921  
INSPECTION &  
FINAL TEST  
N111!

### COIL TAP ARRANGEMENT



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD  
9T18Y4322G88

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009

COPPER CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.


NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency


ASSEMBLED IN MEXICO

Note:

Outline: 303B931SLP075



\*2M000000\*



\*3M000000\*