



GE
 Specialty Transformer
 PO Box 1701
 Ft. Wayne, IN 46801
 (260) 439-2000

GE MODEL #:
9T73C9464G13

Underwriters' Laboratories Inc Listed

RATING:

CU 3PH 60HZ 112.5KVA 480 +2,-4(2.3%TAPS) 208Y/120 NON-SIN K=4 CSL 3

Frame = ST375
 Temp. Rise (C) = 115 Insulation System = 220C
 Average Sound Level (dB) = 50

LOSS DATA @ 100% LOAD:

Core Loss or No Load Loss @ 100% voltage (Watts) =	185
Impedance Loss or Coil Loss @ Rise + 20C reference (Watts) =	<u>1,134.0</u>
Total Loss @ Rise + 20C reference (Watts) =	1,319.0

DIELECTRIC AND PRODUCTION TESTING:

Induce Test @ Twice rated voltage 400 Hz per ANSI C89.2 and NEMA ST-20
 Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz 60 Sec.
 Hipot Test for Low Voltage winding to High Voltage and Ground @ 2500 volts 60 Hz 60 Sec.
 Polarity additive in accordance with ANSI C89.2 and NEMA ST-20

EFFICIENCY:

Efficiencies at reference temperature of Rise + 20C (Calculated).

Load (%)	Efficiency (%)
25	98.7
35	98.9
50	98.9
75	98.7
100	98.5

IMPEDANCE:

Impedance at reference temperature of Rise + 20C (Calculated).

%R =	1.7
%X =	2.9
%Z =	3.4

REGULATION:

Regulation at reference temperature of Rise + 20C (Calculated).

PF	Regulation (%)
1.0	1.7
0.8	3.0