



# Transformer

Catalog Number  
9T77H9872G03


30.0 KVA    60 HZ    3 PH    3.5 % IMP

40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C    Type: QL

Note: Design is based on 30.00KVA & 115C Rise 3.3% Imp.


PRIMARY (H)    480 VOLTS (LINE-LINE)  
SECONDARY (X)    208 VOLTS (LINE-LINE)  
                          120 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE



JUMPER CONNECTION TAP	VOLTS
1	503
2	491
3	480
4	468
5	457
6	446
7	434

### COIL TAP ARRANGEMENT



NET WGT 495 LB    224.5 Kg  
040516    N615!    H372C  
60763    NOG

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R. ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y4317G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL



LISTED 769G

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**

Outline: 3038431SLP072    INSPECTION & FINAL TEST  
Assembled in Mexico    N615!

GE Energy Industrial Solutions

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



\*1M0000000\*



\*3M0000000\*