



# Transformer

NEMA CLASS AA DRY TYPE TRANSFORMER



H1

**Catalog Number**

Type QL

9Q1A015AFAS00A2T00

9T83B2610

15.0 KVA 60 HZ 1 PH 3.6 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


NOG

PRIMARY LINES ON X1-X2	
VOLTS	CONNECT
186	14-X1,13-X2
192	12-X1,11-X2
198	10-X1,9-X2
204	8-X1,7-X2
208	6-X1,5-X2
213	4-X1,3-X2
219	2-X1,1-X2



SECONDARY LINES ON H1-H4	
VOLTS	CONNECT
120	H1-H3,H2-H4
240	H2-H3

NET WGT  
320 LB  
145.2 Kg  
YF171  
58941  
011916

INSPECTION  
&  
FINAL TEST  
N604!



**COIL TAP ARRANGEMENT**



H2 - H1  
H2 - H1  
H4 - H4  
H4 - H4  
X2 - X1  
X2 - X1

H2 - H1  
H2 - H1  
H4 - H4  
H4 - H4  
X2 - X1  
X2 - X1

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

H3 - H4 - H2 - H1  
- X2 - X1 - -

Note: Standard

