



GE Consumer & Industrial
Large Power Transformers
1140 W. INDUSTRIAL PARK DR.
Nogales, AZ 85621

GE MODEL #:
9T73C9876

Underwriters' Laboratories Inc Listed

RATING:

CU 3PH 60HZ 150KVA 480 +2, -4(2.3% TAPS) 208Y/120 CLS-3

Frame = ST376
Temp. Rise (C) = 150 Insulation System = 220C
AVG. Sound Level (dB) = 50

LOSS DATA @ 100% LOAD:

Core Loss or No Load Loss @ 100% voltage (Watts) =	203.0
Impedance Loss or Coil Loss @ Rise + 20C reference (Watts) =	<u>3,882.0</u>
Total Loss @ Rise + 20C reference (Watts) =	4,085.0

DIELECTRIC AND PRODUCTION TESTING:

Induce Test @ Twice rated voltage 400 Hz per UL1561 and NEMA ST-20
Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz 60 Sec.
Hipot Test for Low Voltage winding to High Voltage and Ground @ 2500 volts 60 Hz 60 Sec.
Polarity additive in accordance with UL1561 and NEMA ST-20

EFFICIENCY:

Efficiencies at reference temperature of Rise + 20C (Calculated).

Load (%)	Efficiency (%)
25	98.9
35	98.9
50	98.7
75	98.3
100	97.8

IMPEDANCE:

Impedance at reference temperature of Rise + 20C (Calculated).

%R =	3.0
%X =	4.4
%Z =	5.4

REGULATION:

Regulation at reference temperature of Rise + 20C (Calculated).

PF	Regulation (%)
1.0	3.0
0.8	4.8