



Transformer



Catalog Number Type QL

9T83B2675G15

9T83B2675 9T83B2675 150921KK
 E 303B932AAP075 YNNN 40150220IS-19CQL 1 60AL100109N100.0
 6.6 900 955 240x480(+2,-4 2.30%120/240 E1 I
 09T18Y4322G77615020NN 2FD3TDBGENSALE07831731671201475A1221EAG
 001 N01 NYF175GENSALE0 100.000240x480(+2,-4 2.30%)
 120/240 0705NN N9T18Y43
 22G77TRANSFORMER ENERGY8-NOG H0 0 ASD4


NET WGT
900 LB
408.2 Kg

57742
092115

100.0 KVA 60 HZ 1 PH 6.5 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

NOG





51130000061000000

SECONDARY		PRIMARY	
LINES ON X1-X4	VOLTS	LINES ON H1-H2	VOLTS
VOLTS	CONNECT	VOLTS	CONNECT
	218	436	8-7

INSPECTION
&
FINAL TEST

N539!

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G 77

Outline: 303B932AAP075 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 X4 - X2 X1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

- - H2 - - H1

Note: Standard

X1 - - H1
 X2 - - H1
 X3 X4 - - H2
 X3 X4 - - H2

