



Transformer



Catalog Number **9Q1A025AUAB00A2T00** Type QL

9T83B2711


25.0 KVA

60 HZ

1 PH 5.1 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG



PRIMARY			
UOLTS	CONNECT	UOLTS	CONNECT
108	8-X1,7-X2	216	8-7
114	6-X1,5-X2	222	7-6
120	4-X1,3-X2	228	6-5
126	2-X1,1-X2	234	5-4
		240	4-3
		246	3-2


SECONDARY			
UOLTS	CONNECT	UOLTS	CONNECT
240	H1-H3,H2-H4		
480	H2-H3		

NET WGT
320 LB
145.2 Kg

50095
070115

INSPECTION & FINAL TEST
N5271

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL


H3 - H4 - H2 - H1
- X2 - X1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.


Note: Standard

H1 - - -
H2 - - -
H3 - - -
H4 - - -
X1 - - -
X2 - - -

H1 - - -
H2 - - -
H3 - - -
H4 - - -
X1 - - -
X2 - - -



2M000000



3M000000