




# Transformer

Catalog Number  
9T76H9871G03

15.0 KVA    60 HZ    3 PH    3.4 % IMP  
40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C    Type: QL


PRIMARY (H)    480 VOLTS (LINE-LINE)  
SECONDARY (X)    208 VOLTS (LINE-LINE)  
                          120 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE



JUMPER CONNECTION TAP	VOLTS
1	504
2	492
3	480
4	469
5	455
6	444
7	432

### COIL TAP ARRANGEMENT



NET WGT 315 LB    142.9 Kg  
111617    N746!    H371C  
73771    NOG

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R. ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18V4317G05

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL



LISTED 769G

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**

Outline: 3038431SLP071    INSPECTION & FINAL TEST  
Assembled in Mexico    N746!

GE Energy Industrial Solutions

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



\*1M0000000\*



\*3M0000000\*