



Transformer

Catalog Number
9T76H9873G23


45.0 KVA 60 HZ 3 PH 4.5 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C Type: QL

Note: Design is based on 45.00KVA & 115C Rise 4.5% Imp.


PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 208 VOLTS (LINE-LINE)
 120 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE



JUMPER CONNECTION TAP	VOLTS
1	505
2	493
3	480
4	470
5	455
6	443
7	431

COIL TAP ARRANGEMENT



NET WGT 640 LB 290.3 Kg

041116 N616! H373C
60843 NOG

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R. ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18V4317G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.



LISTED 769G

Outline: 3038431SLP073
Assembled in Mexico

INSPECTION & FINAL TEST
N616!

GE Energy Industrial Solutions

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



1M0000000



3M0000000