



# Transformer




\*1M000000\*

**Catalog Number**  
**9T77H9871G03**

**15.0 KVA    60 HZ    3 PH    3.8 % IMP**  
40 C AMB. 150 C RISE    220 C SYSTEM    IS-19C    Type: QL


PRIMARY (H)    480 VOLTS (LINE-LINE)  
SECONDARY (X)    208 VOLTS (LINE-LINE)  
                          120 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE



JUMPER CONNECTION TAP VOLTS	
TAP	VOLTS
1	503
2	491
3	480
4	468
5	457
6	445
7	433

### COIL TAP ARRANGEMENT



NET WG 1315 LB    142.9 Kg  
082922    N236!    H371C  
90947    NOG

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER    PRIMARY: 10 KV    SECONDARY: 10 KV BIL

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**



LISTED 769G

Outline:  
303B431SLP071

INSPECTION & FINAL TEST  
N236!

GE Energy Industrial Solutions

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



\*2M000000\*



\*3M000000\*