



# Transformer

Catalog Number  
9T77H9872G03

30.0 KVA      60 HZ      3 PH      3.5 % IMP

40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C    Type: QL

Note: Design is based on 30.00KVA & 115C Rise 3.3% Imp.


PRIMARY (H)      480 VOLTS (LINE-LINE)  
SECONDARY (X)    208 VOLTS (LINE-LINE)  
                          120 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y4317G06


BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR      PRIMARY: 10 KV BIL      SECONDARY: 10 KV BIL

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**



JUMPER CONNECTION	
TAP	VOLTS
1	503
2	491
3	480
4	468
5	457
6	446
7	434

### COIL TAP ARRANGEMENT



NET WGT 495 LB    224.5 Kg

033116      N614!      H372C  
60783      NOG



LISTED 769G

Outline: 303B431SLP072  
Assembled in Mexico

INSPECTION & FINAL TEST  
N614!

