



GE Consumer & Industrial
Specialty Transformer
PO Box 1701
Ft. Wayne, IN 46801
(260) 439-2000

GE MODEL #:
9T83B3463G83

Underwriters' Laboratories Inc Listed

RATING:

AL 3PH 60HZ 45.0KVA 480 +2,-4(2.4%TAPS) 208Y/120 NON-SIN K=4

Frame = EE74
Temp. Rise (C) = 80 Insulation System = 220C
Average Sound Level (dB) = 50

LOSS DATA @ 100% LOAD:

Core Loss or No Load Loss @ 100% voltage (Watts) =	387.0
Impedance Loss or Coil Loss @ Rise + 20C reference (Watts) =	<u>820.0</u>
Total Loss @ Rise + 20C reference (Watts) =	1,207.0

DIELECTRIC AND PRODUCTION TESTING:

Induce Test @ Twice rated voltage 400 Hz per ANSI C89.2 and NEMA ST-20
Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz 60 Sec.
Hipot Test for Low Voltage winding to High Voltage and Ground @ 2500 volts 60 Hz 60 Sec.
Polarity additive in accordance with ANSI C89.2 and NEMA ST-20

EFFICIENCY:

Efficiencies at reference temperature of Rise + 20C (Calculated).

Load (%)	Efficiency (%)
35	at least 97.7

IMPEDANCE:

Impedance at reference temperature of Rise + 20C (Calculated).

%R =	1.7
%X =	3.7
%Z =	4.0

REGULATION:

Regulation at reference temperature of Rise + 20C (Calculated).

PF	Regulation (%)
1.0	1.6
0.8	3.3