



# Transformer

by ABB



\*1M000000\*


Catalog Number  
9T77H9873G13

Type QL

45.0 KVA    60 HZ    3 PH    4.6 % IMP  
40 C AMB.    115 C RISE    220 C SYSTEM    IS-19C

### JUMPER CONNECTION TAP VOLTS

1	504
2	492
3	480
4	467
5	455
6	443
7	431




NET WGT  
640 LB  
290.3 Kg  
90696



H373C  
NOG  
062222  
INSPECTION &  
FINAL TEST  
N226I

PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 208 VOLTS (LINE-LINE)  
120 VOLTS (LINE-NEUTRAL)

### COIL TAP ARRANGEMENT



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD  
9T18Y4317G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**

ASSEMBLED IN MEXICO

Note:

Outline: 303B431SLP073

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



\*2M000000\*



\*3M000000\*