



# Transformer

by ABB



\*1M000000\*


Catalog Number 9T77H9875G03 Type QL

112.5 KVA 60 HZ 3 PH 3.6 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

Note: Design is based on 112.5KVA & 115C Rise 3.5% Imp.

JUMPER CONNECTION	TAP VOLTS
1-2	505
2-3	488
3-4	480
4-5	471
5-6	454
6-7	446
7-8	428



NET WGT 1845 LB  
836.9 Kg  
78451


H375C  
NOG  
041421

INSPECTION & FINAL TEST  
N116!



PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 208 VOLTS (LINE-LINE)  
120 VOLTS (LINE-NEUTRAL)

### COIL TAP ARRANGEMENT



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y4322G88

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency


ASSEMBLED IN MEXICO

Note:

Outline: 303B931SLP075



\*2M000000\*



\*3M000000\*