



Transformer



Catalog Number **9T83B2131** Type **QL**

25.0 KVA 60 HZ 1 PH 5.4 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG

| PRIMARY LINES ON X1-X2 | | SECONDARY LINES ON H1-H4 | |
|---------------------------|-------------|-----------------------------|-------------|
| VOLTS | CONNECT | VOLTS | CONNECT |
| 207 | 14-X1,13-X2 | 120 | H1-H3,H2-H4 |
| 213 | 12-X1,11-X2 | 240 | H2-H3 |
| 219 | 10-X1,9-X2 | | |
| 225 | 8-X1,7-X2 | | |
| 230 | 6-X1,5-X2 | | |
| 237 | 4-X1,3-X2 | | |
| 240 | 2-X1,1-X2 | | |

NET WGT

320 LB

145.2 Kg

50028


070115

INSPECTION



&

FINAL TEST

N5271



COIL TAP ARRANGEMENT



LISTED 769G

H1 - - -
H2 - - -
H3 - - -
H4 - - -
X1 - - -
X2 - - -



ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

H3 - H4 - H2 - H1

- X2 - X1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard