



GE Consumer & Industrial
Specialty Transformer
PO Box 1701
Ft. Wayne, IN 46801
(260) 439-2000

GE MODEL #:
9T83B3896

Underwriters' Laboratories Inc Listed

RATING:

AL 3PH 60HZ 150.0KVA 600 +2,-4(2.5%TAPS) 208Y/120

Frame = EE76
Temp. Rise (C) = 150 Insulation System = 220C
Average Sound Level (dB) = 50

LOSS DATA:

Max Core Loss or No Load Loss @ 100% voltage (Watts) =	800.0
Impedance Loss or Coil Loss @ Rise + 20C reference (Watts) =	<u>4,882.7</u>
Total Loss @ Rise + 20C reference (Watts) =	5,682.7

DIELECTRIC AND PRODUCTION TESTING:

Induce Test @ Twice rated voltage 400 Hz per ANSI C89.2 and NEMA ST-20
Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz 60 Sec.
Hipot Test for Low Voltage winding to High Voltage and Ground @ 2500 volts 60 Hz 60 Sec.
Polarity additive in accordance with ANSI C89.2 and NEMA ST-20

EFFICIENCY:

Efficiencies at reference temperature of Rise + 20C (Calculated).

Load (%)	Efficiency (%)
35	at least 98.3

IMPEDANCE:

Impedance at reference temperature of Rise + 20C (Calculated).

%R =	3.1
%X =	5.8
%Z =	6.6

REGULATION:

Regulation at reference temperature of Rise + 20C (Calculated).

PF	Regulation (%)
1.0	3.3
0.8	6