



Transformer



Catalog Number **9T83B2141** Type QL

9T61B38776239T61B3877623 1509221G
 2 303B912HAP278 YNNN 40115220IS-19CQL 3 60AL101034Y225.0
 4 1470 480(+2,-4 2.60%) 208Y/120 E1 M9I
 09T18Y4322688808080NN 10HCUBBGENSALE 53475A1224RAH
 6003N01 NL38AAGENSALE0 225.000480(+2,-4 2.60%)
 208Y/120 0911NN N9T18Y43
 22688TRANSFORMER NON-SIN K=13H0 0

NET WGT
 320 LB
 145.2 Kg
 57846
 092215

25.0 KVA 60 HZ 1 PH 7.4 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG





52091300044018000

SECONDARY LINES ON X1-X4		PRIMARY LINES ON H1-H2	
VOLTS	CONNECT	VOLTS	CONNECT
215	8-H1,7-H2	431	8-7

INSPECTION & FINAL TEST
 N539!

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 - X4 - X2 - X1

- H2 - H1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard

X1
-
X2
-
- H1
-
X4
-
X3
-
- H2
-
X3
-
- H2
-
-

