



# Transformer



\*M0000000\*

Catalog Number      Type QL


9T83B4001G22

20.0 KVA    60 HZ    3 PH 4.4 % IMP


40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C

Note: Design is based on 27.00KVA & 150C Rise 5.9% Imp.

PRIMARY (H)	460 VOLTS (LINE-LINE)
SECONDARY (X)	460 VOLTS (LINE-LINE)
	266 VOLTS (LINE-NEUTRAL)



### COIL TAP ARRANGEMENT



JUMPER CONNECTION

TAP	VOLTS
1-2	483
3-4	460
5-6	438

NET WGT  
334 LB  
151.5 Kg  
9T83B4002G22  
27329  
K0372  
NOG  
013013

INSPECTION  
&  
FINAL TEST  
N305!



ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001      Outline: 303B401AAP072

ALUMINUM CONDUCTOR      PRIMARY: 10 KV BIL      SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

X3 - X2 - X1 - -  
- H3 - H2 - H1

Note: X0 Terminal at the bottom

X3 - X2 - X1 - -  
- H3 - H2 - H1

X3 - X2 - X1 - -  
- H3 - H2 - H1

X0

