



Transformer




Catalog Number **9Q1A015ABAS00A2T00** Type QL

9T83B2220

15.0 KVA 60 HZ 1 PH 3.4 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG



CONDARY		PRIMARY		LINES ON H1-H2		SE
UOLTS	CONNECT	UOLTS	CONNECT	UOLTS	CONNECT	
@120.77A	8-H1,7-H2	414@60.39A	8-7	120@208.33A	X1-	
X3,X2-X4	219@114.16A	6-H1,5-H2	426@58.69A	7-6		
240@104.17A	X2-X3	230@108.70A	4-H1,3-H2	438@		
57.08A	6-5			240@104.17		
A	2-H1,1-H2	450@55.56A	5-4			
				460@54.35A	4-3	
				471@53.08A		
						3-2

NET WGT
320 LB
145.2 Kg
50043
070115

INSPECTION & FINAL TEST
N5271

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R. ENCLOSURE (IP32) WHEN PROVIDED SHIELD. 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 - X4 - X2 - X1
- H2 - H1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard

X1 - - - -
X2 - - - -
- H1 - - - -
X4 - - - -
- H2 - - - -
X3 - - - -

X1 - - - -
X2 - - - -
- H1 - - - -
X4 - - - -
- H2 - - - -
X3 - - - -

2M000000
3M000000