



# Transformer



\*1M000000\*


Catalog Number Type QL

9T83B2231

25.0 KVA 60 HZ 1 PH 6.6 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG





PRIMARY LINES ON H1-H2			
VOLTS	CONNECT	VOLTS	CONNECT
186	8-H1,7-H2	372	8-7
198	6-H1,5-H2	384	7-6
208	4-H1,3-H2	396	6-5
219	2-H1,1-H2	405	5-4
		416	4-3
		426	3-2

SECONDARY LINES ON X1-X4	
VOLTS	CONNECT
120	X1-X3,X2-X4
240	X2-X3

NET WGT  
320 LB  
145.2 Kg  
58411  
120115

INSPECTION  
&  
FINAL TEST  
N549!

### COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP30) RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico


BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 - X4 - X2 - X1  
- H2 - H1 - -


IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard

X1 -  
X2 -  
X3 -  
X4 -  
H1 -  
H2 -



\*2M000000\*



\*3M000000\*