



# Transformer



Catalog Number Type QL


9Q1A050ACAS00A2T00

9T83B2233

50.0 KVA 60 HZ 1 PH 7.9% IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG



PRIMARY LINES ON H1-H2			
VOLTS	CONNECT	VOLTS	CONNECT
186	8-H1, 7-H2	372	8-7
197	6-H1, 5-H2	383	7-6
208	4-H1, 3-H2	395	6-5
216	2-H1, 1-H2	406	5-4
		416	4-3
		426	3-2

SECONDARY LINES ON X1-X4	
VOLTS	CONNECT
120	X1-X3, X2-X4
240	X2-X3

NET WGT

400 LB

181.4 Kg



58059

102315

INSPECTION & FINAL TEST

N543I

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G06

Outline: 303B406AAP072 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

H2 X4 - H1 X1 - -  
- - X3 - - X2

Note: Standard

H2 X4 - H1 X1 - -  
- - X3 - - X2

