



# Transformer



Catalog Number      Type QL

9T83B2606G03

167.0 KVA    50/60 HZ    1 PH    6 % IMP

40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C  
NOG

PRIMARY  
LINES ON H1-H2

VOLTS	CONNECT
360	14-H1,13-H2
373	12-H1,11-H2
380	10-H1,9-H2
387	8-H1,7-H2
400	6-H1,5-H2
413	4-H1,3-H2
420	2-H1,1-H2


SECONDARY  
LINES ON X1-X4

VOLTS	CONNECT
120	X1-X3,X2-X4
240	X2-X3

NET WGT  
1700 LB  
771.1 Kg

55016  
080315

INSPECTION  
&  
FINAL TEST  
N5321



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

### COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G88

Outline: 303B932AAP077    Assembled in Mexico


BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note:



\*2M000000\*



\*3M000000\*