



# Transformer




Catalog Number Type QL

9T83B2652G15

37.5 KVA 60 HZ 1 PH 5.7 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

NOG



PRIMARY LINES ON H1-H2				SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
218	8-H1, 7-H2	229	8-7	240	X1-X3, X2-X4
218	6-H1, 5-H2	229	7-6	240	X2-X3
218	4-H1, 3-H2	229	6-5		
218	2-H1, 1-H2	229	5-4		
		240	4-3		
		240	3-2		

NET WGT

400 LB

181.4 Kg



40530

101415

INSPECTION  
&  
FINAL TEST

N5421

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G06

Outline: 303B406AAP072 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001


ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES


CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

H2 X4 - H1 X1 - -  
- - X3 - - X2

Note: Standard



\*2M0000000\*



\*3M0000000\*

H2 X4 - H1 X1 - -  
- - X3 - - X2