



# Transformer



Catalog Number Type QL


9Q1A015AUAS00A2T00

9T83B2690

15.0 KVA 60 HZ 1 PH 3.1 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG



PRIMARY LINES ON H1-H2				SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
108	8-H1, 7-H2	216	8-7	120	X1-X3, X2-X4
114	6-H1, 5-H2	222	7-6	240	X2-X3
120	4-H1, 3-H2	228	6-5		
126	2-H1, 1-H2	234	5-4		
		240	4-3		
		246	3-2		

NET WGT

320 LB

145.2 Kg



50088

101715

INSPECTION  
&  
FINAL TEST

N5421

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES

CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

X3 - X4 - X2 - X1

- H2 - H1 - -

Note: Standard

X1 - - - - -  
 X2 - - - - -  
 X3 - - - - -  
 X4 - - - - -  
 H1 - - - - -  
 H2 - - - - -

