



# Transformer




\*1M000000\*

**Catalog Number** 9T83B4006G21  
**Type** QL


**63.0 KVA 60 HZ 3 PH 4.8 % IMP**

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C  
*Note: Design is based on 75.00KVA & 150C Rise 5.9% Imp.*

PRIMARY (H) 208 VOLTS (LINE-LINE)  
SECONDARY (X) 230 VOLTS (LINE-LINE)  
133 VOLTS (LINE-NEUTRAL)



### COIL TAP ARRANGEMENT



JUMPER CONNECTION	
TAP	VOLTS
1-2	219
3-4	208
5-6	197

**NET WGT**  
620 LB  
281.2 Kg  
  
55726  
XU374  
NOG  
072915

**INSPECTION & FINAL TEST**  
N531!



ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001 Outline: 303B401AAP074  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Assembled in Mexico

H3 - H2 - H1 - -  
- X3 - X2 - X1

Note: H0 Terminal at the bottom

H3 - H2 - H1 -  
- X3 - X2 - X1  
H3 - H2 - H1 -  
- X3 - X2 - X1

