



Transformer



1M0000000

Catalog Number

Type QL


9Q3A025AFAC00A2T00

9T83B3022G51

25.0 KVA 60 HZ 3 PH 5.4 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

Note: Design is based on 30.00KVA & 150C Rise 6.5% Imp.



JUMPER CONNECTION	
TAP	VOLTS
1	219
2	212
3	208
4	204
5	197
6	193
7	188

NET WGT
334 LB
151.5 Kg


30079
XV372

NOG
111715

INSPECTION
&
FINAL TEST
N547!

PRIMARY (X) 208 VOLTS (LINE-LINE)
 SECONDARY (H) 240 VOLTS (LINE-LINE)
 120 VOLTS (1 PH MIDTAP)

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

REDUCED CAPACITY TAP RATED AT 5% OF 3 PH KVA

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

Outline: 303B401AAP072

ALUMINUM CONDUCTOR

PRIMARY: 10 KV BIL

SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Assembled in Mexico

H3 - H2 - H1 - H4
 - X3 - X2 - X1


Note: Mid-Tap

H4
H1 -
H2 -
H3 -

X1 -
X2 -
X3 -

H4
H1 -
H2 -
H3 -

X1 -
X2 -
X3 -



2M0000000



3M0000000