



Transformer



1M000000

Catalog Number **Type QL**


9Q3A112AEAD00B2T00

9T83B3055G15


112.5 KVA 60 HZ 3 PH 4.5 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

Note: Design is based on 150.0KVA & 150C Rise 5.9% Imp.



COIL TAP ARRANGEMENT



NSALE0 15.000300x
600(+2,-4 2.50%)
120/240

NN
N9T18Y4317G05T
TRANSFORMER E
ENERGY-NOG H0
0

NET WGT
1070 LB
485.4 Kg

43570
XV376
NOG
092115

INSPECTION
&
FINAL TEST
N539!

511



LISTED 769G

Assembled in Mexico

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G07

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001 Outline: 303B401AAP076
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

H3 - H2 - H1 - -
- X3 - X2 - X1


Note: H0 Terminal at the bottom

GE Energy Industrial Solutions

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets TP-1 2002 efficiency

H3 - H2 - H1 -
- X3 - X2 - X1



2M000000

H3 - H2 - H1 -
- X3 - X2 - X1



3M000000

H0