



Transformer

Catalog Number


9T83B3148G15

300.0 KVA 60 HZ 3 PH 2.6 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C Type: Q1

Note: Design is based on 500.0KVA & 150C Rise 4.4% Imp.


| | |
|---------------|--------------------------|
| PRIMARY (H) | 480 VOLTS (LINE-LINE) |
| SECONDARY (X) | 208 VOLTS (LINE-LINE) |
| | 120 VOLTS (LINE-NEUTRAL) |



JUMPER CONNECTION

| TAP | VOLTS |
|-----|-------|
| 1-2 | 500 |
| 2-3 | 490 |
| 3-4 | 480 |
| 4-5 | 470 |
| 5-6 | 460 |
| 6-7 | 440 |
| 7-8 | 430 |

COIL TAP ARRANGEMENT



NET WGT 2265 LB 1027.4 Kg

| | | |
|--------|-------|-------|
| 100815 | N541! | L39AA |
| | 57942 | NOG |



ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G68

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.



Outline: 303B912AAP179
Assembled in Mexico

INSPECTION & FINAL TEST
N541!