



**GE Consumer & Industrial**  
Specialty Transformer  
PO Box 1701  
Ft. Wayne, IN 46801  
(260) 439-2000

**GE MODEL #:**  
**9T83B4012G28**

Underwriters' Laboratories Inc Listed

**RATING:**

AL 3PH 60HZ 220.0KVA 230 +1,-1(5.3%TAPS) 460Y/266

Frame = QF  
Temp. Rise (C) = 150 Insulation System = 220C  
Average Sound Level (dB) = 55

**LOSS DATA:**

Max Core Loss or No Load Loss @ 100% voltage (Watts) =	994.0
Impedance Loss or Coil Loss @ Rise + 20C reference (Watts) =	<u>5,889.1</u>
Total Loss @ Rise + 20C reference (Watts) =	6,883.1

**DIELECTRIC AND PRODUCTION TESTING:**

Induce Test @ Twice rated voltage 400 Hz per ANSI C89.2 and NEMA ST-20

Hipot Test for Low Voltage winding to High Voltage and Ground @ 2500 volts 60 Hz 60 Sec.

Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz 60 Sec.

Polarity additive in accordance with ANSI C89.2 and NEMA ST-20

**EFFICIENCY:**

Efficiencies at reference temperature of Rise + 20C (Calculated).

Load (%)	Efficiency (%)
35	at least 98.5

**IMPEDANCE:**

Impedance at reference temperature of Rise + 20C (Calculated).

%R =	2.5
%X =	4.4
%Z =	5.1

**REGULATION:**

Regulation at reference temperature of Rise + 20C (Calculated).

PF	Regulation (%)
1.0	2.6
0.8	4.7