



Transformer




Catalog Number **9Q1C025AAAS00C2T00** Type QL

9T83C2571G86

25.0 KVA 60 HZ 1 PH 4.6 % IMP

40 C AMB. 80 C RISE 220 C SYSTEM IS-19C

NOG





PRIMARY				SECONDARY			
UOLTS		LINES ON H1-H2		UOLTS		LINES ON X1-X4	
CONNECT	UOLTS	CONNECT	UOLTS	CONNECT	UOLTS	CONNECT	UOLTS
8-H1,7-H2	216	4-3	492	X1-X3,X2-X4	120	8-7	432
6-H1,5-H2	228	7-6	444	X2-X3	240	6-5	456
4-H1,3-H2	240	5-4	468			4-3	480
2-H1,1-H2	252	3-2	480			3-2	492

NET WGT
350 LB
158.8 Kg
53547
090815

INSPECTION & FINAL TEST
N5371

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R. ENCLOSURE (IP32) WHEN PROVIDED SHIELD. 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.


X3 - X4 - X2 - X1
- H2 - H1 - -

Note: Standard

X1 - - -
X2 - - -
X3 - - -
X4 - - -
H1 - - -
H2 - - -



2M000000



3M000000