



# Transformer

Catalog Number


**9T83B3878G15**

**300.0 KVA    60 HZ    3 PH    2.6 % IMP**

40 C AMB.    115 C RISE    220 C SYSTEM    IS-19C    Type: Q1

Note: Design is based on 500.0KVA & 150C Rise 4.4% Imp.


PRIMARY (H)	480 VOLTS (LINE-LINE)
SECONDARY (X)	208 VOLTS (LINE-LINE)
	120 VOLTS (LINE-NEUTRAL)



### JUMPER CONNECTION

TAP	VOLTS
1-2	500
2-3	490
3-4	480
4-5	470
5-6	460
6-7	440
7-8	430



### COIL TAP ARRANGEMENT



NET WGT 2265 LB 1027.4 Kg

100815    N541!    L39AA

57942    NOG



ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G68

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.



LISTED 769G

Outline: 303B912AAP179

Assembled in Mexico

INSPECTION & FINAL TEST

N541!