



Transformer

Catalog Number 9T83C9387G15


9Q3C225AAAZ00B2T00

225.0 KVA 60 HZ 3 PH 5 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C Type: QL

Note: Design is based on 300.0KVA & 150C Rise 6.7% Imp.


PRIMARY (H)	480 VOLTS (LINE-LINE)
SECONDARY (X)	220 VOLTS (LINE-LINE)
	127 VOLTS (LINE-NEUTRAL)



JUMPER CONNECTION

TAP	VOLTS
1-2	502
2-3	490
3-4	480
4-5	466
5-6	454
6-7	442
7-8	429

COIL TAP ARRANGEMENT



NET WGT 3150 LB 1428.8 Kg

090815 N537! YF378

43053 NOG

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G.88

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.



LISTED 769G

Outline: 3038919AAP178
Assembled in Mexico

INSPECTION & FINAL TEST
N537!

