



GE Consumer & Industrial
 Specialty Transformer
 PO Box 1701
 Ft. Wayne, IN 46801
 (260) 439-2000

GE MODEL #:
9T83C9876

Underwriters' Laboratories Inc Listed

RATING:

CU 3PH 60HZ 150.0KVA 480 +2,-4(2.4%TAPS) 208Y/120

Frame = EE76
 Temp. Rise (C) = 150 Insulation System = 220C
 Average Sound Level (dB) = 50

LOSS DATA @ 100% LOAD:

Core Loss or No Load Loss @ 100% voltage (Watts) =	720.0
Impedance Loss or Coil Loss @ Rise + 20C reference (Watts) =	<u>4,235.0</u>
Total Loss @ Rise + 20C reference (Watts) =	4,955.0

DIELECTRIC AND PRODUCTION TESTING:

Induce Test @ Twice rated voltage 400 Hz per ANSI C89.2 and NEMA ST-20
 Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz 60 Sec.
 Hipot Test for Low Voltage winding to High Voltage and Ground @ 2500 volts 60 Hz 60 Sec.
 Polarity additive in accordance with ANSI C89.2 and NEMA ST-20

EFFICIENCY:

Efficiencies at reference temperature of Rise + 20C (Calculated).

Load (%)	Efficiency (%)
35	at least 98.3

IMPEDANCE:

Impedance at reference temperature of Rise + 20C (Calculated).

%R =	2.5
%X =	4.4
%Z =	5.0

REGULATION:

Regulation at reference temperature of Rise + 20C (Calculated).

PF	Regulation (%)
1.0	2.6
0.8	4.6