



# Transformer




Catalog Number **9Q1C050AXAS00B5T00** Type QL

9T83S2573G15

50.0 KVA 60 HZ 1 PH 4.5 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

NOG



PRIMARY			
LINES ON H1-H2			
VOLTS	CONNECT	VOLTS	CONNECT
215	8-H1,7-H2	430	8-7
227	6-H1,5-H2	442	7-6
240	4-H1,3-H2	454	6-5
253	2-H1,1-H2	467	5-4
		480	4-3
		493	3-2

SECONDARY			
LINES ON X1-X4			
VOLTS	CONNECT	VOLTS	CONNECT
120	X1-X3,X2-X4		
240	X2-X3		

NET WGT  
500 LB  
226.8 Kg



55331

072115

INSPECTION  
&  
FINAL TEST

N5301

### COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R. ENCLOSURE (IP32) WHEN PROVIDED SHIELD. 9T18S4317G06

Outline: 303B406SAP073 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 X1 - X2 X4 - -

- - H2 - - H1

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard

X3 X1 - X2 X4 - H1  
 X3 X1 - H2 - - H1  
 X3 X1 - X2 X4 - H1  
 X3 X1 - H2 - - H1

