



Transformer



1M0000000

Catalog Number


TYPE QL

9T83W2573

50.0 KVA 60 HZ 1 PH 4.5 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG




PRIMARY				SECONDARY			
LINES ON H1-H2		LINES ON X1-X4		LINES ON X1-X4		LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
215	8-H1,7-H2	430	8-7	120	X1-X3,X2-X4	240	X2-X3
227	6-H1,5-H2	442	7-6				
240	4-H1,3-H2	454	6-5				
253	2-H1,1-H2	467	5-4				
		480	4-3				
		493	3-2				

NET WGT
500 LB
226.8 Kg
9T40G0007
55331
072115

INSPECTION
&
FINAL TEST
N5301

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18W4317G06

Outline: 303B406MWP073 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 X1 - X2 X4 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

- - H2 - - H1

Note: Standard

X3 X1 - H2 - H1
X2 X4 - H1
X3 X1 - X2 X4 - H1
X3 X1 - H2 - H1

