




Catalog Number TYPE QL

9T83W2611

25.0 KVA 60 HZ 1 PH 6.6 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG



PRIMARY	
UOLTS	CONNECT
186	14-X1,13-X2
192	12-X1,11-X2
198	10-X1,9-X2
204	8-X1,7-X2
208	6-X1,5-X2
213	4-X1,3-X2
219	2-X1,1-X2



SECONDARY	
UOLTS	CONNECT
120	H1-H3,H2-H4
240	H2-H3

NET WGT  
320 LB  
145.2 Kg  
9T40G0007  
58941  
010416

INSPECTION  
&  
FINAL TEST

N6021

COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

H3 - H4 - H2 - H1  
- X2 - X1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard

H1 - H2 - H3 - H4 - X1 - X2

H1 - H2 - H3 - H4 - X1 - X2

