




Drive Isolation Transformer

Catalog Number **9T83B4012G22**

220.0 KVA 60 HZ 3 PH 6 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C Type: Q1




JUMPER CONNECTION

TAP	VOLTS
1-2	481
3-4	460
5-6	436

PRIMARY (H) 460 VOLTS (LINE-LINE)
 SECONDARY (X) 460 VOLTS (LINE-LINE)
 266 VOLTS (LINE-NEUTRAL)

COIL TAP ARRANGEMENT



NET WGT 1590 LB 721.2 Kg

021412 N207! XN377

9T83B4012G 24018 NOG

1M000000

2M000000



ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G79

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

22



Outline: 303B919AAP077
Assembled in Mexico

INSPECTION & FINAL TEST
N207!