



Transformer



1M0000000

Catalog Number TYPE QL

9T83W2612

37.5 KVA 60 HZ 1 PH 9% IMP


40 C AMB. 150 C RISE 220 C SYSTEM IS-19C
NOG

PRIMARY	
LINES ON X1-X2	
VOLTS	CONNECT
186	14-X1,13-X2
192	12-X1,11-X2
198	10-X1,9-X2
204	8-X1,7-X2
208	6-X1,5-X2
213	4-X1,3-X2
219	2-X1,1-X2

SECONDARY	
LINES ON H1-H4	
VOLTS	CONNECT
120	H1-H3,H2-H4
240	H2-H3

NET WGT
320 LB
145.2 Kg
9T40G0007
50048
070115

INSPECTION
&
FINAL TEST
N5271



COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

H3 - H4 - H2 - H1
- X2 - X1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard

H1 - - -
H2 - - -
H3 - - -
H4 - - -
X1 - - -
X2 - - -

