



# Transformer



\*1M0000000\*


Catalog Number TYPE QL

## 9T83W2670G80

15.0 KVA 60 HZ 1 PH 2.9 % IMP

40 C AMB. 80 C RISE 220 C SYSTEM IS-19C

NOG





PRIMARY		SECONDARY	
UOLTS	LINES ON H1-H2 CONNECT	UOLTS	LINES ON X1-X4 CONNECT
216	8-H1,7-H2	432	8-7
228	6-H1,5-H2	444	7-6
240	4-H1,3-H2	456	6-5
252	2-H1,1-H2	468	5-4
		480	4-3
		492	3-2

NET WGT  
320 LB  
145.2 Kg  
9T40G0007  
50069  
070115

INSPECTION & FINAL TEST  
N5271

### COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18W4317G05

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Outline: 303B406MWP071 Assembled in Mexico

X3 - X4 - X2 - X1  
- H2 - H1 - -

Note: Standard

X1 -  
X2 -  
X3 -  
X4 -  
H1 -  
H2 -

X1 -  
X2 -  
X3 -  
X4 -  
H1 -  
H2 -



\*2M0000000\*



\*3M0000000\*