



# Transformer



\*1M000000\*


Catalog Number **9Q5A015AFBL00A2T00** Type **QL**

**9T83B5161**  
**15.0 KVA 50/60 HZ 3 PH 7.9 % IMP**


**40 C AMB. 150 C RISE 220 C SYSTEM IS-19C**

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 400 VOLTS (LINE-LINE)  
231 VOLTS (LINE-NEUTRAL)



### COIL TAP ARRANGEMENT



JUMPER CONNECTION	
TAP	VOLTS
1	217
2	213
3	208
4	202
5	198
6	193
7	187

NET WGT  
240 LB  
108.9 Kg  
  
55837  
XV371  
NOG  
090315

INSPECTION & FINAL TEST N536!



LISTED 769G

Assembled in Mexico

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G11


BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001 Outline: 303B401AAP071  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.


H3 - H2 - H1 - -  
- X3 - X2 - X1

Note:

H3 - H2 - H1 -  
- X3 - X2 - X1  
H3 - H2 - H1 -  
- X3 - X2 - X1  
H0



\*2M000000\*



\*3M000000\*