



# Transformer



\*1M0000000\*

Catalog Number


TYPE QL

## 9T83W2672

37.5 KVA 60 HZ 1 PH 7.7 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG





PRIMARY				SECONDARY	
UOLTS	LINES ON CONNECT	H1-H2 UOLTS	CONNECT	LINES ON UOLTS	X1-X4 CONNECT
216	8-H1, 7-H2	432	8-7	120	X1-X3, X2-X4
228	6-H1, 5-H2	444	7-6	240	X2-X3
240	4-H1, 3-H2	456	6-5		
252	2-H1, 1-H2	468	5-4		
		480	4-3		
		492	3-2		

NET WGT  
320 LB  
145.2 Kg  
9T40G0007  
50069  
070115

INSPECTION & FINAL TEST  
N5271

### COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18W4317G05

Outline: 303B406MWP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 - X4 - X2 - X1

- H2 - H1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard

X1 -  
X2 -  
X3 -  
X4 -  
H1 -  
H2 -

X1 -  
X2 -  
X3 -  
X4 -  
H1 -  
H2 -

