



# Transformer




Catalog Number Type QL

9T83C2291

25.0 KVA 60 HZ 1 PH 5.4 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG





PRIMARY			
LINES ON H1-H2			
UOLTS	CONNECT	UOLTS	CONNECT
258	8-H1,7-H2	516	8-7
273	6-H1,5-H2	531	7-6
288	4-H1,3-H2	546	6-5
303	2-H1,1-H2	561	5-4
		576	4-3
		591	3-2

SECONDARY			
LINES ON X1-X4			
UOLTS	CONNECT	UOLTS	CONNECT
120	X1-X3,X2-X4		
240	X2-X3		

NET WGT  
350 LB  
158.8 Kg  
  
50112  
070115

INSPECTION  
&  
FINAL TEST  
N5271

### COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R. ENCLOSURE (IP32) WHEN PROVIDED SHIELD. 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 - X4 - X2 - X1

- H2 - H1 - -

Note: Standard

X1  
-  
X2  
-  
- H1  
-  
X4  
-  
X3  
-



-  
-  
X2  
-  
- H1  
-  
X4  
-  
X3  
-

