



# Transformer



Catalog Number Type QL

9T83C2517

250.0 KVA 60 HZ 1 PH 7.5 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG

PRIMARY  
LINES ON X1-X2

VOLTS	CONNECT
176	14-X1,13-X2
184	12-X1,11-X2
192	10-X1,9-X2
200	8-X1,7-X2
208	6-X1,5-X2
216	4-X1,3-X2
224	2-X1,1-X2

SECONDARY  
LINES ON H1-H4

VOLTS	CONNECT
120	H1-H3,H2-H4
240	H2-H3


NET WGT  
1960 LB  
889.1 Kg

55018



080315

INSPECTION  
&  
FINAL TEST

N5321



COIL TAP ARRANGEMENT



LISTED 769G


ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G88

Outline: 3038932AAP077 Assembled in Mexico


BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note:



\*2M000000\*



\*3M000000\*