



Transformer




Catalog Number **9T83C2570G83** Type **QL**

15.0 KVA **60 HZ** **1 PH** **2.8 % IMP**

40 C AMB. 80 C RISE 220 C SYSTEM IS-19C

NOG




ELECTROSTATIC GROUND SHIELD IN EACH PHASE

| PRIMARY | | | | SECONDARY | |
|---------|-----------|-------|---------|-----------|-------------|
| UOLTS | CONNECT | UOLTS | CONNECT | UOLTS | CONNECT |
| 216 | 8-H1,7-H2 | 432 | 8-7 | 120 | X1-X3,X2-X4 |
| 228 | 6-H1,5-H2 | 444 | 7-6 | 240 | X2-X3 |
| 240 | 4-H1,3-H2 | 456 | 6-5 | | |
| 252 | 2-H1,1-H2 | 468 | 5-4 | | |
| | | 480 | 4-3 | | |
| | | 492 | 3-2 | | |

NET WGT
350 LB
158.8 Kg
50123
070115

INSPECTION & FINAL TEST
N5271

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

X3 - X4 - X2 - X1
- H2 - H1 - -

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard

X1 - - -
X2 - - -
- H1 - - -
X4 - - -
- H2 - - -
X3 - - -
X3 - - -
- H2 - - -

