



Transformer



Catalog Number Type QL


9Q1C025AXAS01A2T30

9T83C2571G53

25.0 KVA 60 HZ 1 PH 5 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

PRIMARY LINES ON H1-H2				SECONDARY LINES ON X1-X4			
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
216	8-H1, 7-H2	432	8-7	120	X1-X3, X2-X4		
228	6-H1, 5-H2	444	7-6	240	X2-X3		
240	4-H1, 3-H2	456	6-5				
252	2-H1, 1-H2	468	5-4				
		480	4-3				
		492	3-2				

NET WGT

350 LB

158.8 Kg



53548

100715

INSPECTION & FINAL TEST

N541I

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B406AAP071 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

X3 - X4 - X2 - X1

- H2 - H1 - -

Note: Standard

X1 - X2 - X3 - X4 - H1 - H2 - H1 - H2

