

# Transformer

NEMA CLASS AA DRY TYPE TRANSFORMER



\*1M000000\*

Catalog Number


Type QL

9T83C2574G15

75.0 KVA 60 HZ 1 PH 5.3 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

NOG





PRIMARY LINES ON H1-H2				SECONDARY LINES ON X1-X4			
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT		
215	8-H1,7-H2	430	8-7	120	X1-X3,X2-X4		
230	6-H1,5-H2	445	7-6	240	X2-X3		
240	4-H1,3-H2	460	6-5				
250	2-H1,1-H2	470	5-4				
		480	4-3				
		490	3-2				
		500	2-1				

NET WGT  
625 LB  
283.5 Kg  
YF174  
60273  
031816

INSPECTION & FINAL TEST  
N612!

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y4317G06

Outline: 303B406AAP074 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

X3 - X4 - X2 X1 -  
- H2 - H1 - -

Note: Standard

X3 - X4 - H2 - H1



X3 - X4 - H2 - H1

