



Transformer



Catalog Number **9Q1C100AUAB00A2T00** Type QL

9T83C2815

100.0 KVA 60 HZ 1 PH 6% IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

NOG

9T83C25736249T83C2573624 150921IG
 2 303B406AAP073 YNNN 40115220IS-19CQL 1 60CU100109N50.00
 4.5 500 240x480(+2,-4 2.70%120/240 E1 I
 09T18Y4317606535420NN 2FCPUCCGENSALE 01475A809CAG0
 01 N01 NXU173GENSALE0 50.000240x480(+2,-4 2.70%)
 120/240 0705NN N9T18Y43
 17606TRANSFORMER ENERGY8-NOG H0 0

5113000061000000

SECONDARY		PRIMARY	
LINES ON H1-H4	VOLTS CONNECT	LINES ON X1-X2	VOLTS CONNECT
8-7	110	8-X1,7-X2	219

NET WGT
1050 LB


476.3 Kg

57752


092115

INSPECTION
&
FINAL TEST

N539!



COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G 77

Outline: 303B932AAP075 Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

H3 H4 - H2 H1 - -
 - - X2 - - X1

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note: Standard

H3 H4 - X2 - X1
 H2 H1 - X1
 H3 H4 - X2 - X1

